



B4G58N Flexible Copper Braid

By Burndy
Catalog # [B4G58N](#)

Flexible Copper Braid.



General

Catalog Number	B4G58N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810341612
UPC 12 Digit	7818103416122

Dimensions

Dimension - L Length Overall mm	1473 mm
Dimension - Length Overall inch	58.00 in
Length	58 in

Electrical Ratings

Rating - Indoor Amperage	1200
Rating - Outdoor Amperage	1440

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - se211997-01](#)
[Specifications - B4G58N](#)