



# B4G60N Flexible Copper Braid

By Burndy  
Catalog # B4G60N

Flexible Copper Braid.



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## General

Catalog Number	B4G60N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810375266
UPC 12 Digit	7818103752666

## Dimensions

Dimension - L Length Overall	1524 mm
mm	
Dimension - Length Overall	60.00 in
inch	
Length	60 in

## Electrical Ratings

Rating - Indoor Amperage	1200
Rating - Outdoor Amperage	1440

## Certifications And Compliance

Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	360

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - se211997-01](#)  
[Specifications - B4G60N](#)



A Hubbell brand