



## B4G60N Flexible Copper Braid

By Burndy  
Catalog # B4G60N

Flexible Copper Braid.



### General

Catalog Number	B4G60N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810375266
UPC 12 Digit	7818103752666

### Dimensions

Dimension - L Length Overall mm	1524 mm
Dimension - Length Overall inch	60.00 in
Length	60 in

### Electrical Ratings

Rating - Indoor Amperage	1200
Rating - Outdoor Amperage	1440

### Certifications And Compliance

Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	360

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se211997-01](#)
- [Specifications - B4G60N](#)