



B4G7D62G92SV Flexible Copper Braid

By Burndy
Catalog # [B4G7D62G92SV](#)

Silver Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B4G7D62G92SV
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	621945452473

UPC 12 Digit 6219454524733

Dimensions

Dimension - L Length Overall mm	194
Dimension - Length Overall inch	7.62 in
Length	7.62 in
Weight	2.774 lb

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	750

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50060437](#)
[Specifications - B4G7D62G92SV](#)