



B6E17G1TN Flexible Copper Braid

By Burndy

Catalog # B6E17G1TN

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B6E17G1TN
Connector Type	Braid
Material	Copper
UPC	781810507155

UPC 12 Digit 7818105071555

Dimensions

Length 17 in

Certifications And Compliance

Certification - CSA Approved No
Standards - RoHS Compliance CM
Status

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - B6E17G1TN_MODEL-PDF](#)
[3D Models - B6E17G1TN_MODEL-STEP](#)
[3D Models - B6E17G1TN_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B6E17G1TN](#)