



## B6E17G1TN Flexible Copper Braid

By Burndy

Catalog # [B6E17G1TN](#)



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B6E17G1TN
Connector Type	Braid
Material	Copper
UPC	781810507155

UPC 12 Digit 7818105071555

### Dimensions

Length 17 in

### Certifications And Compliance

Certification - CSA Approved No  
Standards - RoHS Compliance CM  
Status

### Logistics

Minimum Pack Quantity 1

### Product Assets

- [3D Models - B6E17G1TN\\_MODEL-PDF](#)
- [3D Models - B6E17G1TN\\_MODEL-STEP](#)
- [3D Models - B6E17G1TN\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - B6E17G1TN](#)