



## B773436L1320 Flexible copper braid 1320.00"x0.30

By Burndy  
Catalog # [B773436L1320](#)

Flexible copper braid 1320.00"x0.30.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B773436L1320
Connector Type	Braid
Material	Copper
UPC	781810507063
UPC 12 Digit	7818105070633

### Dimensions

Dimension - L Length Overall	33528
mm	
Dimension - Length Overall	1320
inch	
Dimension - Width inch	0.3
Length	1320 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[3D Models - B773436L1320\\_MODEL-STEP](#)  
[3D Models - B773436L1320\\_MODEL-PDF](#)  
[3D Models - B773436L1320\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - B773436L1320](#)