



B775936L3960 Flexible tinned copper braid 3960.00"x0.40"

By Burndy
Catalog # B775936L3960

Flexible tinned copper braid 3960.00"x0.40".



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B775936L3960
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
UPC	781810658284
UPC 12 Digit	7818106582844

Dimensions

Dimension - L Length Overall mm	100584
Dimension - Length Overall inch	3960
Dimension - Width inch	0.4
Dimension - Width mm	10 mm
Length	3960 in

Conductor Related

Conductor Size	#36 AWG
----------------	---------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B775936L3960](#)