



## BA10E38M, Vinyl Ring Terminal For 12 - 10 AWG (Tape Mounted)

By Burndy  
Catalog # BA10E38M



Vinyl Ring Terminal For 12 - 10 AWG (Tape Mounted).

### Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

### General

Catalog Number	BA10E38M
Connector Type	Ring Terminal
Insulation Type	Vinyl
Material	Copper
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810028889

### Dimensions

Dimension - Bolt Size fraction 3/8

### Conductor Related

Conductor Size 12 - 10 AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity 1000

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50093722](#)  
[Specifications - BA10E38M](#)