

BA10EF10, Vinyl Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # BA10EF10



Vinyl Fork Terminal For 12 - 10 AWG.

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	BA10EF10
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	BA-EF
UPC	781810026533
UPC 12 Digit	7818100265333

Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	1.07 in
Dimension - Pad Width inch	0.41 in
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.31 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BA14EF10_LineArt](#)
- [Sales Drawings - 50094171](#)
- [Specifications - BA10EF10](#)