



## BA10EF6, Vinyl Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # [BA10EF6](#)



Vinyl Fork Terminal For 12 - 10 AWG.

### Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

### General

Catalog Number	BA10EF6
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	BA-EF
UPC	781810026526
UPC 12 Digit	7818100265266

### Dimensions

Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.28 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.26 in

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BA14EF10\\_LineArt](#)
- [Sales Drawings - 50094171](#)
- [Specifications - BA10EF6](#)