

BA14E10M, Vinyl Ring Terminal For 16 - 14 AWG (Tape Mounted)

By Burndy
Catalog # [BA14E10M](#)



Vinyl Ring Terminal For 16 - 14 AWG (Tape Mounted).

Features

- Vinyl Ring Terminal banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

General

Catalog Number	BA14E10M
Connector Type	Ring Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810028964
UPC 12 Digit	7818100289644

Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	0.85 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.26 in

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50093722](#)
- [Specifications - BA14E10M](#)