

BA14EL10, Vinyl Locking Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [BA14EL10](#)



Vinyl Locking Fork Terminal For 16 - 14 AWG.

Application

For Fast Installation And Security

General

Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	BA-EL, Locking
UPC	781810026939
UPC 12 Digit	7818100269399

Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	15/79
Dimension - Hole Size inch	0.19 in
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.36 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.31 in

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094176](#)