



## BA16E14M, Vinyl Ring Terminal For 22 - 16 AWG (Tape Mounted)

By Burndy  
Catalog # [BA16E14M](#)



Vinyl Ring Terminal For 22 - 16 AWG (Tape Mounted).

### General

Connector Type	Ring Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLU <sup>TM</sup>
Type	Ring Tongue
UPC	781810029091
UPC 12 Digit	7818100290911

### Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	0.99 in
Dimension - Pad Width inch	0.40 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.36 in

### Conductor Related

Conductor - Copper Solid Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor - Copper Str Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	2000
-----------------------	------

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50093722](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BA16E14M-SPEC-EN | REV 1/2024