

# BA16EZ6, Vinyl Flanged Fork Terminal For 22 - 16 AWG

By Burndy  
Catalog # BA16EZ6



Vinyl Flanged Fork Terminal For 22 - 16 AWG.

## Features

- Flanged Fork Tongue design allows for fast installation as screw only has to be loosened for termination
- Flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

## Application

For Fast Installation And Security

## General

Catalog Number	BA16EZ6
Connector Type	Flanged Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Flange Fork
UPC	781810026786
UPC 12 Digit	7818100267866

## Dimensions

Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.83 in
Dimension - Pad Width inch	0.28 in

Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.23 in

## Conductor Related

Conductor - Copper Solid Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor - Copper Str Size Range	20 AWG - 22 AWG; 16 AWG - 18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BA10EZ8\\_LineArt](#)
- [Sales Drawings - 50094185](#)
- [Specifications - BA16EZ6](#)