



BB024L108 Flexible Copper Braid

By Burndy
Catalog # [BB024L108](#)

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB024L108
Connector Type	Braid
Material	Copper
UPC	781810226698

UPC 12 Digit 7818102266988

Dimensions

Length 108 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	EX
Status	

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2960

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50049474](#)
- [Specifications - BB024L108](#)