



BB024L12G18 Flexible Copper Braid

By Burndy
Catalog # [BB024L12G18](#)

Flexible Copper Braid.



General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 1 |
| Plated | Y |
| UPC | 781810106709 |
| UPC 12 Digit | 7818101067099 |

Dimensions

| | |
|---------------------------------|-------|
| Dimension - L Length Overall mm | 305 |
| Dimension - Length Overall inch | 12 |
| Length | 12 in |

Electrical Ratings

| | |
|-----------------|------|
| Amperage Rating | 93 A |
|-----------------|------|

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 30021690](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BB024L12G18-SPEC-EN | REV 5/2024