



BB024L12GGKIT Flexible Copper Braid

By Burndy
Catalog # BB024L12GGKIT

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number BB024L12GGKIT
Connector Type Braid

Material	Copper
UPC	781810675410
UPC 12 Digit	7818106754100

Dimensions

Length	12 in
--------	-------

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	UI
Status	

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BB024L12GGKIT](#)