



## BB024L12LT516 Flexible Copper Braid

By Burndy  
Catalog # BB024L12LT516

Flexible Copper Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB024L12LT516
Connector Type	Braid
Material	Copper
Material - Ferrules	N
UPC	621945458420
UPC 12 Digit	6219454584200

### Dimensions

Dimension - L Length Overall mm	321
Dimension - Length Overall inch	12.62
Length	12.62 in

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50066562](#)
- [Specifications - BB024L12LT516](#)