



BB024L12LT58 Flexible Copper Braid

By Burndy
Catalog # BB024L12LT58

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB024L12LT58
Material - Ferrules	N
UPC	621945462335

Dimensions

Dimension - L Length Overall	333
mm	
Dimension - Length Overall	13.1
inch	
Length	12 in

Certifications And Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Logistics

Carton Quantity	50
Minimum Pack Quantity	100
Pallet Quantity	4500

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50084383](#)
[Specifications - BB024L12LT58](#)