



BB024L18LT14B Flexible Copper Braid

By Burndy
Catalog # BB024L18LT14B

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

| | |
|----------------|---------------|
| Catalog Number | BB024L18LT14B |
| Connector Type | Rope lay |
| Material | Copper |
| UPC | 781810674734 |
| UPC 12 Digit | 7818106747344 |

Dimensions

| | |
|--------|---------|
| Length | 18.5 in |
|--------|---------|

Certifications And Compliance

| | |
|------------------------------|-----|
| Certification - CSA Approved | Yes |
| Standards - RoHS Compliance | CM |
| Status | |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 4800 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50053108](#)
- [Specifications - BB024L18LT14B](#)