



BB024L6G30 Flexible Copper Braid

By Burndy

Catalog # BB024L6G30

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB024L6G30
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810661888

Dimensions

Dimension - L Length Overall	168
mm	
Dimension - Length Overall	6.6
inch	
Length	6 in

Electrical Ratings

Amperage Rating	93 A
-----------------	------

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	14800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50036372](#)
[Specifications - BB024L6G30](#)



A Hubbell brand