

BB024L6T14 Flexible Copper Braid

By Burndy

Catalog # BB024L6T14

Flexible Copper Braid, 6.00 in L, Flexible copper braid jumpers designed to take up linear expansion and contraction.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB024L6T14
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810552520
UPC 12 Digit	7818105525200

Dimensions

Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in

Dimension - N inch	0.5 in
Dimension - Stud Size inch	1/4
Length	6 in

Electrical Ratings

Rating - Indoor Amperage	93
Rating - Outdoor Amperage	93

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	150
Minimum Pack Quantity	1
Pallet Quantity	2250

Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_B_lineart](#)
[Sales Drawings - 50007330](#)
[Specifications - BB024L6T14](#)