

BB024L72 Flexible Copper Braid

By Burndy
Catalog # [BB024L72](#)

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB024L72
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	781810340967

UPC 12 Digit 7818103409677

Dimensions

Dimension - L Length Overall mm	1829
Dimension - Length Overall inch	72
Length	72 in

Certifications And Compliance

Standards - RoHS Compliance Status	EX
---------------------------------------	----

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2960

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50049474](#)
[Specifications - BB024L72](#)