

## BB024L72G56TN Flexible Copper Braid

By Burndy  
Catalog # [BB024L72G56TN](#)

Tin Plated Ferrules.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB024L72G56TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	781810550458
UPC 12 Digit	7818105504588

### Dimensions

Dimension - L Length Overall	1829
mm	
Dimension - Length Overall	72
inch	
Length	72 in

### Electrical Ratings

Rating - Indoor Amperage	93 A
--------------------------	------

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50001430](#)  
[Specifications - BB024L72G56TN](#)