



BB024L8LT14 Flexible Copper Braid

By Burndy
Catalog # BB024L8LT14

Flexible Copper Braid.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB024L8LT14
Connector Type	Braid
Material	Copper
Plated	Y
UPC	781810674673
UPC 12 Digit	7818106746733

Dimensions



Dimension - L Length Overall	216
mm	
Dimension - Length Overall	8.5
inch	
Length	8.5 in

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	6000

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50047632](#)
- [Specifications - BB024L8LT14](#)