



## BB024L9G60 Tinned copper braid 9"x0.60"x0.10"

By Burndy  
Catalog # BB024L9G60

Tinned copper braid 9"x0.60"x0.10".



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB024L9G60
Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810568446
UPC 12 Digit	7818105684466

### Dimensions

Dimension - L Length Overall mm	229
Dimension - Length Overall inch	9
Dimension - Width inch	0.6
Dimension - Width mm	15 mm
Length	9 in

### Electrical Ratings

Amperage Rating	93 A
-----------------	------

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	UI

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - BB024L9G60](#)