



BB024SS18T14TN Stainless steel braid with HYLUG™ 18"x0.43"x0.04"

By Burndy

Catalog # [BB024SS18T14TN](#)



Stainless steel braid with HYLUG™ 18"x0.43"x0.04".

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB024SS18T14TN
Connector Type	Braid
Material	Stainless Steel
Material - Ferrules	Copper
Physical Attribute - Number of Braids	1

UPC	781810643693
UPC 12 Digit	7818106436933

Dimensions

Dimension - L Length Overall mm	457
Dimension - Length Overall inch	18
Dimension - Width inch	0.43
Dimension - Width mm	11 mm
Length	18 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BB024SS18T14TN](#)