



## BB024SSL6LT38, Stainless Steel Flexible Braid

By Burndy

Catalog # [BB024SSL6LT38](#)

Flexible Stainless Steel Braid



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB024SSL6LT38
Connector Type	Braid
Material	Stainless Steel
UPC	781810674826
UPC 12 Digit	7818106748266

### Dimensions

Dimension - L Length Overall	168.4
mm	
Dimension - Length Overall	6.63
inch	
Length	6.63 in

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	5550

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50049484](#)
- [Specifications - BB024SSL6LT38](#)