



## BB031ML24T14TN, One-Hole Braid, 24" long, 1/4" stud, tin plated

By Burndy

Catalog # [BB031ML24T14TN](#)

One-Hole Braid, 31 kcmil, 24", 1/4" stud, tin plated, approx AWG Size #6



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number BB031ML24T14TN

UPC 621945650411

### Dimensions

Dimension - Stud Size inch	1/4"
Length	24 in
Thickness	0.09 in
Width	0.59 in

### Conductor Related

Conductor Size	#6 AWG
Wire Size	16mm <sup>2</sup>

### Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50121361](#)  
[Specifications - BB031ML24T14TN](#)