



## BB038SSL5D91T12, Stainless Steel Flexible Braid

By Burndy

Catalog # [BB038SSL5D91T12](#)

Flexible Stainless Steel Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB038SSL5D91T12
Connector Type	Braid
Material	Stainless Steel
UPC	621945453838

UPC 12 Digit

6219454538388

### Dimensions

Dimension - L Length Overall mm	150
Dimension - Length Overall inch	5.91
Length	5.91 in

### Certifications And Compliance

Certification - CSA Approved No

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50062177](#)  
[Specifications - BB038SSL5D91T12](#)