



## BB038SSL7D87T12, Flexible Stainless Steel Braid

By Burndy

Catalog # [BB038SSL7D87T12](#)

Flexible Stainless Steel Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

|                |                 |
|----------------|-----------------|
| Catalog Number | BB038SSL7D87T12 |
| Connector Type | Braid           |
| Material       | Stainless Steel |
| UPC            | 621945453845    |

UPC 12 Digit

6219454538455

### Dimensions

|                                    |         |
|------------------------------------|---------|
| Dimension - L Length Overall<br>mm | 200     |
| Dimension - Length Overall<br>inch | 7.8     |
| Length                             | 7.87 in |

### Certifications And Compliance

Certification - CSA Approved No

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50062177](#)  
[Specifications - BB038SSL7D87T12](#)



A Hubbell brand