



BB038SSL7D87T12, Flexible Stainless Steel Braid

By Burndy

Catalog # [BB038SSL7D87T12](#)



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB038SSL7D87T12
Connector Type	Braid
Material	Stainless Steel
UPC	621945453845

UPC 12 Digit 6219454538455

Dimensions

Dimension - L Length Overall mm	200
Dimension - Length Overall inch	7.8
Length	7.87 in

Certifications And Compliance

Certification - CSA Approved No

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50062177](#)
[Specifications - BB038SSL7D87T12](#)



A Hubbell brand