

## BB048L24T38 Flexible Copper Braid

By Burndy  
Catalog # [BB048L24T38](#)



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB048L24T38
Connector Type	Braid
Material	Copper
Plated	Y
UPC	621945439436
UPC 12 Digit	6219454394366

### Dimensions

Dimension - L Length Overall	610
mm	
Dimension - Length Overall	24
inch	
Length	24 in

### Electrical Ratings

Amperage Rating	93 A
-----------------	------

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	3000

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50048729](#)  
[Specifications - BB048L24T38](#)