



BB059ML24T38TN, One-Hole Braid, 24" long, 3/8" stud, tin plated

By Burndy

Catalog # [BB059ML24T38TN](#)

One-Hole Braid, 59 kcmil, 24", 3/8" stud, tin plated, approx AWG Size #3

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number BB059ML24T38TN



UPC 621945650817

Dimensions

| | |
|----------------------------|---------|
| Dimension - Stud Size inch | 3/8" |
| Length | 24 in |
| Thickness | 0.13 in |
| Width | 0.91 in |

Conductor Related

| | |
|----------------|-------------------|
| Conductor Size | #3 AWG |
| Wire Size | 30mm ² |

Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 50121364](#)

[Specifications - BB059ML24T38TN](#)