



BB067L1200 Flexible Copper Braid

By Burndy

Catalog # [BB067L1200](#)

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB067L1200
Connector Type	Braid
Material	Copper
Plated	Y
UPC	781810510551
UPC 12 Digit	7818105105511

Dimensions

Dimension - L Length Overall mm	30480
Dimension - Length Overall inch	1200
Length	1200 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BB067L1200_MODEL-PDF](#)
- [3D Models - BB067L1200_MODEL-IGES](#)
- [3D Models - BB067L1200_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50049476](#)
- [Specifications - BB067L1200](#)