

BB077L60 Flexible Copper Braid

By Burndy
Catalog # BB077L60

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB077L60
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	781810082782
UPC 12 Digit	7818100827822

Dimensions

Dimension - L Length Overall	1524 mm
mm	
Dimension - Length Overall	60 in
inch	
Length	60 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	296

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50049477](#)
[Specifications - BB077L60](#)