



BB100L12D80G21TN Flexible Copper Braid

By Burndy

Catalog # [BB100L12D80G21TN](#)

Flexible Copper Braid with Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB100L12D80G21TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	781810649411
UPC 12 Digit	781810649411

Dimensions

Dimension - L Length Overall	300 mm
mm	
Dimension - Length Overall	11.8 in
inch	
Length	12.8 in

Electrical Ratings

Amperage Rating	300 A
-----------------	-------

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	28
Pallet Quantity	2100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50002016](#)
- [Specifications - BB100L12D80G21TN](#)