



BB100L12T34 Flexible Copper Braid

By Burndy
Catalog # [BB100L12T34](#)

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	621945460829
UPC 12 Digit	6219454608299

Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12 in
Length	12 in

Electrical Ratings

Amperage Rating	290 A
-----------------	-------

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	25
Pallet Quantity	4500

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50068181](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BB100L12T34-SPEC-EN | REV 5/2024