



BB100L20D69G21TN Flexible Copper Braid

By Burndy

Catalog # [BB100L20D69G21TN](#)

Tin Plated Copper Braid 19.69 inches long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

| | |
|---------------------|------------------|
| Catalog Number | BB100L20D69G21TN |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Plated | Y |
| UPC | 621945443556 |
| UPC 12 Digit | 6219454435566 |

Dimensions

| | |
|------------------------------|----------|
| Dimension - L Length Overall | 500 mm |
| Dimension - Length Overall | 19.69 in |
| Length | 20.69 in |

Electrical Ratings

| | |
|-----------------|-------|
| Amperage Rating | 300 A |
|-----------------|-------|

Certifications And Compliance

| | |
|------------------------------|-----|
| Certification - CSA Approved | Yes |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 3600 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50002016](#)
- [Specifications - BB100L20D69G21TN](#)



A Hubbell brand