



## BB100L24D60G21TN Flexible Copper Braid

By Burndy  
Catalog # [BB100L24D60G21TN](#)

Tin Plated Copper Braid 23.60 inches long.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	781810649428
UPC 12 Digit	7818106494288

### Dimensions

Dimension - L Length Overall mm	599 mm
Dimension - Length Overall inch	23.6 in
Length	24.6 in

### Electrical Ratings

Amperage Rating	300 A
-----------------	-------

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2100

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50002016](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BB100L24D60G21TN-SPEC-EN | REV 1/2024