

BB100L36N Flexible Copper Braid

By Burndy

Catalog # [BB100L36N](#)

Tin Plated Copper Braid 36 inches long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB100L36N
Connector Type	Braid
Material	Copper
UPC	781810512838
UPC 12 Digit	7818105128388

Dimensions

Dimension - L Length Overall	916 mm
mm	
Dimension - Length Overall	36.00 in
inch	
Length	36 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

Product Assets

[3D Models - BB100L36N_MODEL-IGES](#)

[3D Models - BB100L36N_MODEL-STEP](#)

[3D Models - BB100L36N_MODEL-PDF](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 30012108](#)

[Specifications - BB100L36N](#)