



BB100L50G15TN Flexible Copper Braid

By Burndy
Catalog # [BB100L50G15TN](#)

Tin Plated Copper Braid 50 inches long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB100L50G15TN
Connector Type	Braid
Material	Copper
Plated	Y
UPC	781810508336
UPC 12 Digit	7818105083366

Dimensions

Dimension - L Length Overall	1270 mm
Dimension - Length Overall	50.00 in
Length	50 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30004740](#)
[Specifications - BB100L50G15TN](#)