



# BB100L56D12G21TN Flexible Copper Braid

By Burndy  
Catalog # BB100L56D12G21TN

Tin Plated Copper Braid 55 inches long.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB100L56D12G21TN
Connector Type	Braid
Material	Copper
Plated	Y
UPC	621945452749
UPC 12 Digit	6219454527499

### Dimensions

Dimension - L Length Overall	1397 mm
mm	
Dimension - Length Overall	55 in
inch	
Length	56.12 in

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	10
Minimum Pack Quantity	5
Pallet Quantity	1680

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50002016](#)  
[Specifications - BB100L56D12G21TN](#)



A Hubbell brand