



BB100L59G21TN Flexible Copper Braid

By Burndy
Catalog # [BB100L59G21TN](#)

Tin Plated Copper Braid 58 inches long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB100L59G21TN
Connector Type	Braid
Material	Copper
Plated	Y
UPC	621945452756
UPC 12 Digit	6219454527566

Dimensions

Dimension - L Length Overall	1473 mm
mm	
Dimension - Length Overall	58 in
inch	
Length	59 in

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	5
Pallet Quantity	1050

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50002016](#)
- [Specifications - BB100L59G21TN](#)