



BB139ML24T12TN, One-Hole Braid, 24" long, 1/2" stud, tin plated

By Burndy

Catalog # [BB139ML24T12TN](#)

One-Hole Braid, 139 kcmil, 24", 1/2" stud, tin plated, approx AWG Size 2/0



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number BB139ML24T12TN

UPC 621945651012

Dimensions

| | |
|----------------------------|---------|
| Dimension - Stud Size inch | 1/2" |
| Length | 24 in |
| Thickness | 0.16 in |
| Width | 1.18 in |

Conductor Related

| | |
|----------------|-------------------|
| Conductor Size | 2/0 AWG |
| Wire Size | 70mm ² |

Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 50121367](#)

[Specifications - BB139ML24T12TN](#)



A Hubbell brand