



BB139ML24T38TN, One-Hole Braid, 24" long, 3/8" stud, tin plated

By Burndy

Catalog # [BB139ML24T38TN](#)

One-Hole Braid, 139 kcmil, 24", 3/8" stud, tin plated, approx AWG Size 2/0



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number BB139ML24T38TN

UPC 621945650985

Dimensions

Dimension - Stud Size inch	3/8"
Length	24 in
Thickness	0.16 in
Width	1.18 in

Conductor Related

Conductor Size	2/0 AWG
Wire Size	70mm ²

Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50121367](#)
[Specifications - BB139ML24T38TN](#)