



BB154L36 Flexible Copper Braid

By Burndy

Catalog # [BB154L36](#)

Flexible Copper Braid 36 inches long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB154L36
Connector Type	Braid
Material	Copper
UPC	781810444504

UPC 12 Digit 7818104445044

Dimensions

Dimension - L Length Overall mm	914 mm
Dimension - Length Overall inch	36 in
Length	36 in

Certifications And Compliance

Standards - RoHS Compliance NC
Status

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50049478](#)
[Specifications - BB154L36](#)