



## BB154L60 Flexible Copper Braid

By Burndy  
Catalog # [BB154L60](#)

Flexible Copper Braid 60 inches long.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB154L60
Connector Type	Braid
Material	Copper
UPC	781810437940

UPC 12 Digit 7818104379400

### Dimensions

Dimension - L Length Overall mm	1524 mm
Dimension - Length Overall inch	60 in
Length	60 in

### Certifications And Compliance

Standards - RoHS Compliance UI  
Status

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50049478](#)  
[Specifications - BB154L60](#)