



## BB154L7800 Flexible Copper Braid

By Burndy

Catalog # [BB154L7800](#)

Flexible Copper Braid 7800 inches long.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BB154L7800
Connector Type	Braid
Material	Copper
UPC	781810202753
UPC 12 Digit	7818102027533

### Dimensions

Dimension - L Length Overall	198120 mm
mm	
Dimension - Length Overall	7800 in
inch	
Length	7800 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	650
-----------------------	-----

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50049478](#)
- [Specifications - BB154L7800](#)



A Hubbell brand